

Univox® PI S-X5

The next generation of loop drivers

Features

- 5 year warranty
- 1U high and ½ width (19" rack) for side by side mounting to save rack space
- Parametric Metal-Loss-Control for various types of metallic influences
- Built-in System diagnostics, to isolate a system malfunction
- Programmable XLR, RCA and screw terminal input connectors
- Dual Action AGC for unsurpassed intelligibility
- Low frequency masking filter for voice enhancement
- 50-100 V input
- Voice alarm system input that overrides all other input signals
- Convection cooled for silent reliable operation
- 10 W output for connecting a speaker to monitor/verify driver activity
- Front panel placed controls for easy installer access
- Recessed controls to prevent tampering
- Rack mounting kit

Applications

Univox PLS-X5 is suitable for lecture halls, auditoriums, churches, gate areas and larger rooms.

Space and power efficiency


PLS-X series is the most efficient professional loop drivers available. The units are only 1U high and ½ widths, making it possible to mount two drivers in one single 19" rack mount. Univox PLS-X series uses a 90 % efficient electronic transformer. Energy waste in a conventional power supply is comparably 8-9 times higher. Weight is reduced by use of significantly less copper and other metals than conventional loop drivers, leaving a much smaller carbon footprint. PLS-X loop drivers produces an amazingly clear sound which is not possible using conventional toroid transformers as modulation distortion is unavoidable.

The self-diagnostic system

When activated, input connection, AGC, pre and power driver and consistency of loop conductor will be diagnosed. The diagnostics will indicate which systems are operational and which are not. The built-in signal generator, which is part of the self-diagnostic system, can be used to set just the output level if another signal source is not available.

Enhanced metal compensation

Univox PLS-X's are equipped with a unique Parametric MLC (Metal Loss Correction) to fine tune for the effects of metal loss. It allows the installer to further compensate for metal attenuations effects and not just simply by increasing level from one default frequency. See graph.



Coverage Area in m²/ft²

60 V 61 42 6 7 11 64 11 11 17 / E		
No Metal Loss	Metal Loss	High Metal Loss
Free field, up to 25m/ 82ft segment width	4.5 dB attenuation, max 7m/22ft segment width	8 dB attenuation, max 4m/13ft segment width
450/ <i>4800</i>	50/ <i>540</i> *	_**
600/ <i>6500</i>	100/1000*	_**
900/ <i>9700</i>	780/8400	400/4300
	No Metal Loss Free field, up to 25m/82ft segment width 450/4800 600/6500	No Metal Loss Free field, up to 25m/ 82ft segment width 450/4800 600/6500 Metal Loss 4.5 dB attenuation, max 7m/22ft segment width 50/540* 100/1000*

^{*} Coverage area limited by max segment width

^{**} Univox SLS is recommended



Induction Loop Output RMS 125 ms

36.5 Vpp/12.9 Vrms Max Drive Voltage

Max Drive Current 9.5 Arms

Power

Input 2

Power supply 110-240 VAC primary switched class V electronic power supply

Back panel interface

Balanced XLR Input 1

Programmable Bass Cut Filter@150 Hz - Speech/Flat, Line/Mic,

Phantom Power +12 VDC On/Off

Sensitivity: -50 dBu (2.5 mVrms) to +10 dBu (2.6 Vrms)

Balanced Phoenix Screw Terminal Block

Dip switch programmable: Low Cut Filter@150 Hz - Flat/Speech: line/50-100V connection On/Off; Override On/Off (Input 3 signals higher than -6 dB above AGC-knee overrides all other input signals)

Line sensitivity: -15 dBu (50 mVrms) to +20.6 dBu (8.3 Vrms)

Input 3 Unbalanced RCA and Phoenix Screw Terminal Block

Sensitivity: -24 dBu (30 mVrms) to +16.2 dBu (5 Vrms)

Out Pre-amplifier Buffered output to connect multiple drivers In Power-amplifier Input for connectiong multiple drivers

Monitor control Recessed trim potentiometer for 10W speaker and 3.5mm front

panel headphone output

Monitor connection Phoenix Screw Terminal Block

10W speaker monitor output; 24V power output; Remote LED

diagnostic output

Front panel interface

4 LED indicators (-18 dB to +12 dB), recessed trim potentiometers Input 1-3

Metal loss control Switchable frequency knee point (100 Hz, 500 Hz,1 kHz, 2 kHz)

Adjustable gain slope from 0 to 4 dB/octave

System Diagnosis Checks Input connection, AGC, Pre and Power driver and Loop

conductor with a pulsed 1 kHz signal (built in signal generator)

On/Off switch to operate system, single LED indication

Loop Current Control Recessed trim pot; 4 LED output level indicator (0-9dB)

Peak / Clipping LED indicates if signal is peaking/clipping Monitor 3.5 mm jack to monitor loop with headset Power indicator LED indicates correct power connection

Other Systems and Functions

Frequency responce 75-6800 Hz Distortion

Dual Action AGC Dynamic Range: > 50-70 dB (+1.5 dB)

Attack time: 2-500 ms, Release time: 0.5-20 dB/s

Cooling Internal cooling element

Physical

½ width 1U 19" rack mount Size

Width 210 mm, Depth 255 mm, Height 44 mm

Mounting options 1U 19" rack mount (brackets included)* or Freestanding

* Brackets for mounting side-by-side with another PLS-X, needs to

be ordered separately.

Weight Weight incl. power supply and box 2.65 kg 217500 Part No



Accessories and tools

Univox Listener

This easy to use loop listener indicates field strength levels of 400 mA/m and 200 mA/m in accordance with IEC 60118-4. It is an essential tool for the facility manager as well as an alternative assistive listening device for



Univox FSM 2.0

the Hard of Hearing.

Engineered for simplicity, the Univox FSM 2.0 is a microprocessor controlled field strength meter featuring a simple 5 step programme for commissioning loop systems to the performance standard IEC 60118-4.




Copper foil

This insulated copper foil is only 0.25 mm thick and is easily concealed under most floor finishes. It is ideal for multi loop and Super loop installations.



Univox Loop Designer

Univox Loop Designer is a tool to aid in the design of Hearing Loop Systems in accordance with the International Induction Loop System performance standard IEC 60118-4.



Copyright © Bo Edin AB ols-x5-br-gb



The User Guide, Installation Guide and Certificate of Conformity are available on both of our websites for download.